



# BGA gel flux series IF 8300

INTERFLUX®  
ELECTRONICS N.V.



Technical data IF 8300 series  
Ver: 2.1 30-05-13

Page 1



## No-clean, halide free tacky gel flux

### Description:

**Interflux® IF 8300** is a no-clean, halide free tacky gel flux.


The flux provides resin-like rheological properties. It is available in different viscosities for different applications.

The **IF 8300** series can be applied by printing, dispensing or by brush.

The **IF 8300** gel flux series is compatible with both lead-free and lead containing alloys.

The flux exhibits good wetting on virtually all surface finishes including OSP, NiAu, I-Sn...etc.

The residues are minimal and transparent and do not require any cleaning.



### Physical and chemical properties:

State	: viscous
Colour	: yellow
Odour	: sweet, mild
Halide content	: none
pH (5% aq.sol)	: 3
IPC/ EN	: RE L0

### More information:

Reflow profile	2
Profile recommendations SnPb alloys	2
Profile recommendations Pb free alloys	3
Test results	4
Packaging	4

### Key advantages:

- True halogen free
- Classification to IPC and EN: **RE L0**
- Excellent wetting on I-Sn, Ni/Au, OSP, Ag/Pd

## Properties

	IF 8300	IF 8300-4	IF 8300-6
Flash point	158 °C	144 °C	137 °C
Solubility in water	insoluble	insoluble	insoluble
Auto-ignition point	> 370 °C	> 370 °C	> 370 °C
Specific gravity	1,032 g/ml	1,020 g/ml	1,013 g/ml
Viscosity at 20 °C	± 210.000 cPs	± 70.000 cPs	± 25.000 cPs



## Reflow profile

### General description

In general a soak profile is advised and may be used when temperature differences across a board, due to a high mix of components or large board sizes, need to be levelled out. Or when the number of voids, if present because of material combination, need to be decreased.

When soldering in air the profile's peak temperature should occur within a frame time of maximum 300sec or 5 minutes from the profile's starting point.

The correct conveyor speed (m/min) can be calculated by dividing the total chamber length (m) of the heating zones by the desired process time (min). Soldering under nitrogen has fewer

limitations.

When soldering an assembly in a lead free solder process, care must be taken not to overheat components especially when using air convection or IR ovens.

It is very important to know the temperature limitations of the components used on the board.

To get a good thermal mapping of the board it is advised to use thermocouples and a thermal measuring tool. Measure on small outline, big outline and temperature sensitive components. Measure on the board side near the conveyor chain, in the middle of the board and close to, or on heat sinks.

## Profile recommendations SnPb and SnPbAg alloys

### Preheat

From room temperature until  $\pm 150^{\circ}\text{C}$  at a rate of 1-3  $^{\circ}\text{C}/\text{s}$ . Faster rates could result in component cracking due to absorbed moisture evaporating.

zone is used to level out temperature differences on a board. It is often used in IR ovens and on boards with a big diversity of components and Cu distribution.

### Ramp to reflow

From  $150^{\circ}\text{C}$  to melting point.

Maximum  $4^{\circ}\text{C}/\text{s}$  because of different thermal expansion coefficients inside the components.

### Reflow

Peak temperature related to component specifications, in general from 205-


$230^{\circ}\text{C}$ . Time above liquidus: In general 30s-90s

### Cool down

Maximum  $4^{\circ}\text{C}/\text{s}$  because of different thermal expansion coefficients of the materials involved.

### Soak zone

Around  $150^{\circ}\text{C}$ . A soak





## Profile recommendations SAC and SnAg alloys

### **Preheat**

From room temperature until  $\pm 150^{\circ}\text{C}$  at a rate of 1-3  $^{\circ}\text{C}/\text{s}$ . Faster rates could result in component cracking due to absorbed moisture evaporating.

### **Soak zone**

Around  $170^{\circ}\text{C}$ . A soak

zone is used to level out temperature differences on a board. It is often used in IR ovens and on boards with a big diversity of components and Cu distribution.

### **Ramp to reflow**

From  $170^{\circ}\text{C}$  to peak temperature.

Maximum  $4^{\circ}\text{C}/\text{s}$  because of different thermal expansion coefficients inside the components.


### **Reflow**

Peak temperature related to component specifications, in general from  $230^{\circ}\text{C}$

to  $245^{\circ}\text{C}$ . Time above liquidus: In general 30s-90s

### **Cool down**

Maximum  $4^{\circ}\text{C}/\text{s}$  because of different thermal expansion coefficients of the materials involved.





## Test results

conform EN 61190-1-2(2002) and IPC J-STD-004A

Property	Result	Method
<b>Chemical</b>		
copper mirror	<b>pass</b>	J-STD-004A IPC-TM-650 2.3.32
qualitative halide		
silver chromate (Cl, Br)	<b>pass</b>	J-STD-004A IPC-TM-650 2.3.33
acid value by titration	<b>28,9</b>	mg KOH/g
<b>Environmental</b>		
SIR test	<b>pass</b>	J-STD-004A IPC-TM-650 2.6.3.3

## Gebinde:

The IF8300-series is available in the following packaging:

### IF8300

- 5cc syringe with and without plunger
- 10 cc syringe with and without plunger
- 30 cc syringe with and without plunger
- 30 cc jar
- 100 cc jar
- 310 cc cartridge
- 1 kg bucket

### IF8300-4

- 30cc jar with brush
- 1kg bucket

### IF8300-6

- 30cc jar with brush
- 1kg bucket

Trade name : BGA Gel Fluxes IF 8300 series, IF 8300, IF 8300-4, IF 8300-6

D i s c l a i m e r

Because Interflux® Electronics N.V. cannot anticipate or control the many different conditions under which this information and our products may be used, we do not guarantee the applicability or the accuracy of this information or the suitability of our products in any given situation. Users of our products should make their own test to determine the suitability of each such product for their particular purposes. The product discussed is sold without such warranty, either express or implied.

Copyright:  
**INTERFLUX®** ELECTRONICS

Please consult the latest version of this document on:  
[www.interflux.com](http://www.interflux.com)

This document in another language?:  
[www.interflux.com](http://www.interflux.com)

